

Raster Link 7

Improves reproducibility of special effects (such as transparency) of PDF data

Increases RIP processing speed of PDF data by 25% on average Prints out the variable data by Variable print function

JigLink function enables jig management by bar code



· Mimaki Taro .0001 · Mimaki Hanako · 0002 .0003





## Improves efficiency

## **Automation of printing processes**

Adaptable to "Mimaki Device Language (MDL)" to realize automation of printing processes

Using MDL commands allows you to automate printer control, job management, and workpiece conveying device operation from an external device









Please note that machine failures due to MDL commands may not be covered by our warranty

#### ■Specifications

_ <b>o</b> poo	outionio		
Item		UJF-7151 plusli	
Print head		On-demand piezo head	
Print resolution		600 dpi / 900 dpi / 1200 dpi / 1800 dpi	
	Туре	UV curable ink LH-100 / LUS-120 / LUS-350 / MUH-100-Si / PR-200	
Ink	Color	C/M/Y/K/Lc/Lm/W/Pr/Cl/Si	
	Ink supply	1 L / 250 ml / 200 ml bottle supply method*	
Maximum printable area		710 × 510 mm	
	Size	710 × 530 mm (28 × 20 in) or less	
Media	Thickness	153 mm (6 in) or less	
	Weight	30 kg (66 lb) or less	
Interface		USB2.0 / Ethernet (10 BASE / 100 BASE / 1000 BASE)	
Certifications		VCCI-Class A, FCC-Class A, IEC62368-1, ETL CE Mark (EMC Directive, Low Voltage Directive, Machinery Directive) CB Report, RoHS, REACH, ENERGY STAR, EAC, RCM	
Power supply		Single phase AC 100-240 V, 50/60 Hz	
Power consumption		1,300 VA or less	
	Temperature	15 - 30 degC (59 - 86 degF)	
	Humidity	35-65% Rh (No condensation)	
Operational environment	Recommended temperature range for stable operation	20 - 25 degC (68 - 77 degF)	
	Allowable range of temperature change	±10 degC/h or less	
	Dust level	Equivalent to a general office floor level	
Dimensions (W×D×H)		2,203 × 1,572 × 1,293 mm (87 × 62 × 51 in)	
Installation area		2,803 × 2,580 mm (110 × 102 in)	
Main unit weight		330 kg (728 lb) Base stand weight is included.	
RIP Software		RasterLink7 (provided as standard software)	

#### ■Options

Item	Item code	Remark				
Pilot lamp	OPT-J0398	Indicator light				
Vacuum unit	OPT-J0419	Additional vacuum				
UJF-7151 plusII OP Ionizer	OPT-J0518	To eliminate static electricity				
UJF-7151 plusii Full cover OP	OPT-J0520	For noise reduction, safety, dust control				
OP Air filter	OPT-J0515					
Kebab MkII L	OPT-J0433	For printing on cylindrical materials				

#### Supply

Item		Item No.	Remark
	Cyan	LH100-C-BA	
	Magenta	LH100-M-BA	
	Yellow	LH100-Y-BA	
	Black	LH100-K-BA	1L bottle
	White	LH100-W-BA	
LH-100	Clear	LH100-CL-BA	
	Light Cyan	LH100-LC-BA	
	Light Magenta	LH100-LM-BA	
	Cvan	LH100-C-B2	
	Magenta	LH100-M-B2	250ml bottle
	Yellow	LH100-Y-B2	
	Black	LH100-K-B2	
	White	LH100-W-B2	
	Clear	LH100-CL-B2	
	Light Cyan	LH100-LC-B2	
	Light Magenta		
	Cyan	LUS12-C-BA	
	Magenta	LUS12-M-BA	
	Yellow	LUS12-Y-BA	
	Black	LUS12-K-BA	1L bottle
	White	LUS12-W-BA	
	Clear	LUS12-CL-BA	
	Light Cyan	LUS12-LC-BA	
LUS-120	Light Magenta	LUS12-LM-BA	
LUS-120	Cyan	LUS12-C-B2	
	Magenta	LUS12-M-B2	250ml bottle
	Yellow	LUS12-Y-B2	
	Black	LUS12-K-B2	
	White	LUS12-W-B2	
	Clear	LUS12-CL-B2	
	Light Cyan	LUS12-LC-B2	
	Light Magenta	LUS12-LM-B2	
	Cyan	LUS35-C-BA	
	Magenta	LUS35-M-BA	41.1.40
LUS-350	Yellow	LUS35-Y-BA	
	Black	LUS35-K-BA	1L bottle
	White	LUS35-W-BA	
	Clear	LUS35-CL-BA	
MUH-100-Si	Silver	MUH-10-Si	1 bottle
IJ Primer PR-200		PR200-Z-BA	1L bottle
		PR200-Z-B2	250ml bottle
Flushing liquid 07		FL007-Z-BA	1L bottle
Maintenance 15 100ml bottle		ML015-Z-B1	100ml bottle
Maintenance 15 kit		ML015-Z-K1	Maintenance kit with 2 pcs. of 100ml bottle
ODEENGUADO	Gold-certified inks	400	

<sup>\*</sup> GREENGUARD Gold-certified inks are LH-100 and LUS-120.

## Inks and substrates:

•As physical properties of ink (adhesion, weather resistance etc.) are different depending on media, please be sure

•Depending on the application, primers, other surface treatment or surface protection such as lamination may be

## ▲ Safety notice:

This product is equipped with UV irradiation equipment. Please pay attention to the following notes in order to use safely.

\*Do not look directly into the UV light source nor place your hand, or expose your skin directly to the UV light source. Depending upon print mode, some VOC emittance from printed parts not yet cured and hardened may occur
 In addition, please be sure to read and follow the instructions and guidelines of the manual carefully.

Some of the samples in this catalog are artificial renderings. Specifications, design and dimensions stated in this catalog may be subject to change without notice (for technical improvements, etc). The corporate names and merchandise names written on this catalog are the trademark or registered trademark of the respective corporations. Inkjet printers print using extremely fine dots, so colors may very slightly vary after replacement of the printing heads. Also note that if using multiple printer units, colors could vary slightly from one unit to other unit due to slight individual differences.



#### MIMAKI ENGINEERING CO., LTD.

2182-3 Shigeno-Otsu, Tomi-city, Nagano 389-0512, Japan

### Mimaki Global Network

Singapore MIMAKI SINGAPORE PTE. LTD.

MIMAKI USA, INC. MIMAKI BRASIL COMERCIO E IMPORTAÇÃO LTDA MIMAKI INDIA PRIVATE LIMITED MIMAKI ENGINEERING (TAIWAN) CO.,LTD.

Europe MIMAKI EUROPE B.V. Indonesia PT. MIMAKI INDONESIA Australia MIMAKI AUSTRALIA PTY, LTD. SHANGHAI MIMAKI TRADING CO.,LTD. Thailand MIMAKI (THAILAND) CO.,LTD.

**INDUSTRIAL PRODUCTS** 

**High-Performance** Flatbed UV Inkjet Printer



# UJF-7151 plusⅢ









<sup>\*</sup> For LH-100, LUS-120 and PR-200, 1 L and 250 ml bottles are available.

\* Only the 1 L bottle is available for the LUS-350, and only the 200 ml bottle for the MUH-100-Si.